

There are 18 Caen C207 16-channel discriminators being used as level translator from NIM to ECL. These 18 modules output on ECL ribbon cable to the FTDC modules in the DAQ crate. FTDC modules have 64 channels fed on 4 16-channel cables.

Level Translator	FTDC Module slot/Input
1	TDC1-A
2	TDC1-B
3	TDC1-C
4	TDC1-D
5	TDC2-A
6	TDC2-B
7	TDC2-C
8	TDC2-D
9	TDC3-A
10	TDC3-B
11	TDC3-C
12	TDC3-D
13	TDC4-A
14	TDC4-B
15	TDC4-C
16	TDC4-D
17	TDC5-A
18	TDC5-B