

8330D



Silver Conductive Epoxy Adhesive

8330D is an electrically conductive, silver-filled 2-part epoxy adhesive. It is smooth, non-sagging, thixotropic, and bonds well to a wide variety of substrates.

This product allows for quick, cold-soldering repairs. It can also be used as a solder replacement for bonding heat-sensitive electronic components, or for making conductive connections where soldering is not an option, such as when bonding to glass, soft metals, or plastics.

8330D is highly filled to maximize electrical conductivity. For a more economical version, use 8331D. For a longer working life, use 8330S.



Features and Benefits

- Creates strong permanent electrical connections
- Cures at room temperature
- SVHC free
- Excellent adhesion to many substrates
- Room temperature storage
- Long shelf life

Available Packaging

Cat. No.	Packaging	Net Vol.	Net Wt.
8330D-19G	2 Syringe kit	6 mL	19.4 g
8330D-160G	2 Jar kit	50 mL	162 g

Contact Information

MG Chemicals, 1210 Corporate Drive
Burlington, Ontario, Canada L7L 5R6

Email: support@mgchemicals.com

Phone: North America: +(1)800-340-0772

International: +(1) 905-331-1396

Europe: +(44)1663 362888

Cured Properties

Resistivity	$5.3 \times 10^{-4} \Omega \cdot \text{cm}$
Hardness	84 D
Tensile Strength	8.3 N/mm ²
Compressive Strength	75 N/mm ²
Lap Shear (stainless steel)	3.6 N/mm ²
(aluminum)	2.6 N/mm ²
Glass Transition Temperature (T_g)	40 °C
CTE Prior T_g	63 ppm/°C
CTE After T_g	363 ppm/°C
Thermal Conductivity @ 25 °C	2 W/(m·K)
Service Temperature Range	-50–150 °C

Usage Parameters

Working Time	20 min
Service Cure	65 min @ 22 °C
Mix Ratio by Volume	1:1
Mix Ratio by Weight	1.1:1

Uncured Properties

Mixed Density	3.22 g/mL
Shelf Life	3 y
Viscosity @ 25 °C	(A) 698 Pa·s
	(B) Thixotropic

Application Instructions

Read the product SDS and Application Guide for more detailed instructions before using this product (downloadable at www.mgchemicals.com).

Recommended Preparation

Clean the substrate with Isopropyl Alcohol, MG #824, so the surface is free of oils, dust, and other residues.

Syringe

1. Twist and remove the cap from the syringe.
Do not discard cap.
2. Measure 1 part by volume of A.
3. Measure 1 part by volume of B.
4. Dispense material on a mixing surface or container, and thoroughly mix parts A and B together.
5. To stop the flow, pull back on the plunger.
6. Clean nozzle to prevent contamination and material buildup.
7. Replace the cap on the syringe.

Can or Jar

1. Stir each part individually to re-incorporate material that may have separated.
2. Measure 1.1 part by weight of A.
3. Measure 1 part by weight of B.
4. Thoroughly mix parts A and B together.
5. Apply adhesive to the application area.

Cure Instructions

Allow to cure at room temperature for 6 hours, or cure the adhesive in an oven at one of these time/temperature options:

- 10 min @ 65 °C
- 5 min @ 80 °C

Storage and Handling

Store between 16 and 27 °C in a dry area, away from sunlight (see SDS). To maximize shelf life, recap product firmly when not in use.

Disclaimer

This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.